


GRID CONTROL RECTIFIER TUBE

TANTALUM ANODE AND XENON GAS FILLING



BOTTOM VIEW OF BASE

| | | |
|--|--|------------|
| Maximum Rated Anode Current | | |
| D-c. Meter Value-Continuous | | 1.0 amp |
| Averaging Time | | 4.5 secs |
| Oscillograph Peak-Continuously recurring | | 8.0 amps |
| Max. Instantaneous Short Circuit Current (0.1sec.) | | 77 amps |
| Peak Forward Voltage (Max. Instantaneous) | | 1000 volts |
| Peak Inverse Voltage (Max. Instantaneous) | | 1250 volts |
| Max. Commutation Factor (V _{usec} x A/usec) | | 0.15 |
| at a maximum initial inverse voltage of 500 volts | | |

| | | |
|------------------------|--|----------------|
| Filament | | |
| Voltage | | 2.5 volts |
| Current | | 6.3 ± 0.8 amps |
| Heating Time (minimum) | | 25 secs |

| | | |
|-----------------------------|--|----------|
| Average Arc Drop | | |
| Average Tube | | 8 volts |
| Highest Tube at end of life | | 14 volts |

| | | |
|--|--|----------|
| Anode Starting Voltage (D. C.) @ +4V d-c. grid voltage | | |
| Average Tube | | 25 volts |
| Highest Tube | | 75 volts |

| | | |
|-------------------------------------|--|-------------------|
| Grid Characteristics | | |
| Critical Grid Voltage @ 1000 p.f.v. | | -4.5 ± 2.0 volts |
| Critical Grid Current | | Less than 5 uamps |
| Grid-Anode Capacitance | | approx. 1 uuf |
| Grid-Filament Capacitance | | approx. 10 uuf |

| | | |
|-------------------------------|--|-----------|
| Maximum Negative Grid Voltage | | 100 volts |
|-------------------------------|--|-----------|

| | | |
|-------------------|--|---------------------|
| Deionization Time | | Less than 500 usecs |
|-------------------|--|---------------------|

| | | |
|----------------------------|--|----------------|
| Ambient Temperature Limits | | -55° to +75° C |
|----------------------------|--|----------------|


| | | |
|-------------------|--|-----|
| Mounting Position | | Any |
|-------------------|--|-----|

| | | |
|--------------------|--|-----------------------|
| Overall Dimensions | | 1-9/16" x 4-1/4" max. |
| Weight | | 3 ozs. |

| | | |
|---------------------------|--|---------------------------------------|
| Connections | | |
| Filament, Grid, and Anode | | Metal medium 4-pin bayonet base A4-10 |

The filament must be lit before drawing d-c. load current.
 The anode is designed to operate at red heat when under full load.
 All of the above values are for returns to the filament transformer center tap.

The Engineering Manual contains additional information which should be considered in the circuit design.



ELECTRONS, INCORPORATED
 127 Sussex Avenue
 Newark 3, New Jersey